

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P300473-31M Martenne

Martenne Collection Two-Light Matte Black Modern Farmhouse Vanity Light

**Category:** Bath & Vanity  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Housing  
**Glass/Shade:** Clear Seeded Glass Cone



Width: 14 in  
Extends: 7 in  
Height: 8-1/2 in  
H/CTR: 4-7/8 in (glass facing up)

Clear Seeded Glass Cone  
Width: 4-5/8 in  
Height: 5-1/16 in

| MOUNTING   | ELECTRICAL                | LAMPING  | ADDITIONAL INFORMATION     |
|--|---------------------------|--|----------------------------|
| Wall mounted   | 6 inches of wire supplied | (2) Medium Base (E26) Socket   | cULus Damp Location Listed |
| Mounting plate for outlet box included   | 120 VAC                   | Lamp Type<br>Incandescent: 60-watt MAX per socket<br>LED: 12.5-watt MAX per socket | 1-year Limited Warranty    |
| Fixture can be installed with glass facing up or down                            |                           | Fully dimmable with dimmable bulbs.  |                            |
| Canopy covers a standard 4" recessed outlet box: 6.68" W., 4.5" ht., 0.81" depth |                           |  |                            |