

Project:

Fixture Type:

Location:

P300474-196

Martenne

Contact:

Martenne Collection Three-Light Aged Bronze Modern Farmhouse Vanity Light

Category: Bath & Vanity

Finish: Aged Bronze (Hand Painted) **Construction:** Steel Housing

Glass/Shade: Clear Seeded Glass Cone

Width: 24 in Extends: 7 in Height: 8-1/2 in

H/CTR: 4-7/8 in (glass facing up)

Clear Seeded Glass Cone

Width: 4-5/8 in Height: 5-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 6.68" W., 4.5" ht., 0.81" depth		Fully dimmable with dimmable bulbs.	