

Project:			
Fixture Type:			
Location:			
Contact:			



P300474-31M

Martenne

Martenne Collection Three-Light Matte Black Modern Farmhouse Vanity Light

Category: Bath & Vanity Finish: Matte Black (Painted) Construction: Steel Housing

Glass/Shade: Clear Seeded Glass Cone

Width: 24 in Extends: 7 in Height: 8-1/2 in

H/CTR: 4-7/8 in (glass facing up)

Clear Seeded Glass Cone

Width: 4-5/8 in Height: 5-1/16 in

	MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
	Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
	Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
ı	Fixture can be installed with glass facing up or down		LED: 12.5-watt MAX per socket	
			Fully dimmable with dimmable	
	Canopy covers a standard 4" recessed outlet box: 6.68" W., 4.5" ht., 0.81" depth		bulbs.	