

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P300475-31M Martenne

Martenne Collection Four-Light Matte Black Modern Farmhouse Vanity Light

**Category:** Bath & Vanity  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Housing  
**Glass/Shade:** Clear Seeded Glass Cone

Width: 31-7/8 in  
Extends: 7 in  
Height: 8-1/2 in  
H/CTR: 4-7/8 in (glass facing up)

Clear Seeded Glass Cone  
Width: 4-5/8 in  
Height: 5-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 6.68" W., 4.5" ht., 0.81" depth			