

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300480-009 Cassell

Cassell Collection One-Light Brushed Nickel Matte Black Luxe Industrial Bath & Vanity Light

Category: Bath & Vanity

Finish: Brushed Nickel (Plated) with Matte Black accent

Construction: Steel Housing

Glass/Shade: Clear Glass Cone



Width: 4-3/4 in
Extends: 6-5/8 in
Height: 9-1/8 in
H/CTR: 6-1/8 in (glass facing up)

Clear Glass Cone
Width: 4-3/4 in
Height: 5-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 4.56" W., 6" ht., 4.56" depth			