



Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P300480-163 Cassell

Cassell Collection One-Light Vintage Brass Matte Black Luxe Industrial Bath & Vanity Light

**Category:** Bath & Vanity  
**Finish:** Vintage Brass (Plated) with Matte Black accent  
**Construction:** Steel Housing  
**Glass/Shade:** Clear Glass Cone



Width: 4-3/4 in  
 Extends: 6-5/8 in  
 Height: 9-1/8 in  
 H/CTR: 6-1/8 in (glass facing up)

Clear Glass Cone  
 Width: 4-3/4 in  
 Height: 5-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 4.56" W., 6" ht., 4.56" depth			