

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P300481-009
Cassell

Cassell Collection Two-Light Brushed Nickel Matte Black Luxe Industrial Bath & Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated) with Matte Black accent
Construction: Steel Housing
Glass/Shade: Clear Glass Cone



Width: 14-1/2 in
 Extends: 6-5/8 in
 Height: 9-1/8 in
 H/CTR: 6-7/8 in (glass facing up)

Clear Glass Cone
 Width: 4-3/4 in
 Height: 5-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 6" W., 4.56" ht., 0.81" depth			