

Project:			
Fixture Type:			
Location:			



## P300483-163

## Cassell

Contact:

Cassell Collection Four-Light Vintage Brass Matte Black Luxe Industrial Bath & Vanity Light

Category: Bath & Vanity

Finish: Vintage Brass (Plated) with Matte Black accent

Construction: Steel Housing Glass/Shade: Clear Glass Cone

Width: 33-7/8 in Extends: 6-5/8 in Height: 9-1/8 in

H/CTR: 6-7/8 in (glass facing up)

Clear Glass Cone Width: 4-3/4 in Height: 5-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 6" W., 4.56" ht., 0.81" depth		Fully dimmable with dimmable bulbs.	