

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300485-015 Lexie

Lexie Collection Two-Light Polished Chrome Contemporary Vanity Light

Category: Bath & Vanity
Finish: Polished Chrome (Plated)
Construction: Steel Housing
Glass/Shade: Etched Opal Glass Bell



Width: 14 in
Extends: 6-5/8 in
Height: 11 in
H/CTR: 8-1/2 in (glass facing up)

Etched Opal Glass Bell
Width: 5-1/8 in
Height: 6-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth			