

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P300485-31M**  
**Lexie**

Lexie Collection Two-Light Matte Black Contemporary Vanity Light

**Category:** Bath & Vanity  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Housing  
**Glass/Shade:** Etched Opal Glass Bell



Width: 14 in  
Extends: 6-5/8 in  
Height: 11 in  
H/CTR: 8-1/2 in (glass facing up)

Etched Opal Glass Bell  
Width: 5-1/8 in  
Height: 6-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth			