

Project:

Fixture Type:

Location:

Contact:

P300486-015 Lexie

Lexie Collection Three-Light Polished Chrome Contemporary Vanity Light

Category: Bath & Vanity

Finish: Polished Chrome (Plated)
Construction: Steel Housing
Glass/Shade: Etched Opal Glass Bell



Width: 22 in Extends: 6-5/8 in Height: 11 in

H/CTR: 8-1/2 in (glass facing up)

Etched Opal Glass Bell Width: 5-1/8 in Height: 6-3/4 in

	0 211		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 100-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht. 4.87" depth		bulbs.	