

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P300488-197
Quillan

Quillan Collection One-Light White Plaster Transitional Bath & Vanity Light

Category: Bath & Vanity
Finish: White Plaster (Hand Painted) with Soft Gold accent
Construction: Steel Housing
Glass/Shade: Clear Glass Bell

Width: 5 in
 Extends: 6-5/8 in
 Height: 8-1/2 in
 H/CTR: 6 in (glass facing up)

Clear Glass Bell
 Width: 4-13/16 in
 Height: 5-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1.62" ht., 5.12" depth			



Includes two sets of socket rings in White Plaster and Soft Gold finishes