

Project:		
Fixture Type:		
Location:		
Contact:		



## P300490-197 Quillan

Quillan Collection Three-Light White Plaster Transitional Bath & Vanity Light

Category: Bath & Vanity

Finish: White Plaster (Hand Painted) with Soft Gold accent

**Construction:** Steel Housing **Glass/Shade:** Clear Glass Bell

Width: 23-7/8 in Extends: 6-5/8 in Height: 8-1/2 in

H/CTR: 6 in (glass facing up)

Clear Glass Bell Width: 4-13/16 in Height: 5-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1.62" ht., 5.12" depth		bulbs.	





Includes two sets of socket rings in White Plaster and Soft Gold finishes