

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



**P300490-204**  
**Quillan**

Quillan Collection Three-Light Soft Gold Transitional Bath & Vanity Light

**Category:** Bath & Vanity  
**Finish:** Gold Ombre (Hand Painted) with Soft Gold accent  
**Construction:** Steel Housing  
**Glass/Shade:** Clear Glass Bell

Width: 23-7/8 in  
Extends: 6-5/8 in  
Height: 8-1/2 in  
H/CTR: 6 in (glass facing up)

Clear Glass Bell  
Width: 4-13/16 in  
Height: 5-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1.62" ht., 5.12" depth			



Includes two sets of socket rings in Gold Ombre and Soft Gold finishes