PROGRESS LIGHTING



Project:

Fixture Type:

Location:

Contact:



P300491-204 Quillan

Quillan Collection Four-Light Soft Gold Transitional Bath & Vanity Light

Category: Bath & Vanity Finish: Gold Ombre (Hand Painted) with Soft Gold accent Construction: Steel Housing Glass/Shade: Clear Glass Bell

Width: 33-5/8 in Extends: 6-5/8 in Height: 8-1/2 in H/CTR: 6 in (glass facing up)

Clear Glass Bell Width: 4-13/16 in Height: 5-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cETLus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1.62" ht., 5.12" depth		Fully dimmable with dimmable bulbs.	



Includes two sets of socket rings in Gold Ombre and Soft Gold finishes