

Project:
Fixture Type:
Location:
Contact:

## Captarent LED

Damp Location Listed PROGRESS LED

### **Description:**

Captarent Collection 60 in. x 36 in. Rectangular Illuminated Integrated LED White Color Selectable Modern Mirror

### **Specifications:**

- · Mirror Glass Rectangle
- · Dimmable to 10% brightness
- Fixture covers a standard 4" recessed outlet box
- · Americans With Disabilities Act (ADA) compliant

#### **Performance:**

Input Power	92 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2150/23 (LM-79)
at 3000K setting	
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2022

# P300492-030-CS





### **Dimensions:**

Width: 60 in Extends: 2-3/16 in Height: 36 in



# Captarent LED

· Damp Location Listed PROGRESS LED

### **Photometrics:**

P300492-030-CS

ELECTRICAL DATAP300492-030-CSInput Voltage120 VACInput Frequency60 HzTHD<20%</td>

EMI/RFI FCC Title 47, Part 15, Class B

Operating Temperature -30 °C to 30

Dimming Yes\*

Over-voltage, over-current, short-circuit protected \*See Dimming Notes for more information