


Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P300496-205 Pinellas

Two-Light Bath & Vanity

Category: Bath & Vanity
Finish: Soft Gold (Painted)
Construction: Steel Construction
Glass/Shade: Opal Glass Cone

Width: 15 in
 Extends: 5-3/4 in
 Height: 9-3/4 in
 H/CTR: 7-1/8 in

Opal Glass Cone
 Width: 4.5 in
 Height: 5-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cETLus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	