



Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P300499-009 Tanner

One-Light Bath & Vanity

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cone
 VT



Width: 5-1/8 in
 Extends: 6-3/4 in
 Height: 7-1/8 in
 H/CTR: 4-1/2 in (glass facing up)

Etched Glass Cone
 Width: 4-5/8 in
 Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs	