

Project:			
Fixture Type:			
Location:			
Contact:			



P300501-009

Tanner

Three-Light Bath & Vanity

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cone

VT

Width: 22 in Extends: 6-1/2 in Height: 7-1/8 in

H/CTR: 4-1/2 in (glass facing up)

Etched Glass Cone Width: 4-5/8 in Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass		Incandescent: 60-watt MAX per socket	
facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs	