



Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_



## P300502-009 Tanner

Four-Light Bath & Vanity

**Category:** Bath & Vanity  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Etched Glass Cone  
 VT

Width: 31-1/8 in  
 Extends: 6-1/2 in  
 Height: 7-1/8 in  
 H/CTR: 4-1/2 in (glass facing up)

Etched Glass Cone  
 Width: 4-5/8 in  
 Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs	