

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300502-31M Tanner

Four-Light Bath & Vanity

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Glass Cone

Width: 31-1/8 in
Extends: 6-1/2 in
Height: 7-1/8 in
H/CTR: 4-1/2 in (glass facing up)

Etched Glass Cone
Width: 4-5/8 in
Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs	