

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_



**P300505-009**  
**Spenser**

Three-Light Bath & Vanity

**Category:** Bath & Vanity  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Opal Glass Bell

Width: 23-3/8 in  
 Extends: 5-1/2 in  
 Height: 7-5/8 in  
 H/CTR: 5-3/8 in (glass facing up)

Opal Glass Bell  
 Width: 4-1/8 in  
 Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.12" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	