

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300506-191 Spenser

Four-Light Bath & Vanity

Category: Bath & Vanity
Finish: Brushed Gold (Plated)
Construction: Steel Construction
Glass/Shade: Opal Glass Bell

Width: 32-7/8 in
Extends: 5-1/2 in
Height: 7-5/8 in
H/CTR: 5-3/8 in (glass facing up)

Opal Glass Bell
Width: 4-1/8 in
Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.12" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	