

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P3363-09 Wisten

The three-light linear Wisten Collection features linear bar with suspended tapered etched glass shades. Cool and modern with a casual flair, Wisten provides a signature look to any room. Three-light wall or ceiling mount directional-track light in a Brushed Nickel finish.

- Sweeping arms framing elegant, tapered glass shades.
- Cool and modern with a casual flair.
- Provides a signature, universal look to any room.
- Meets California Title 24.

Category: Directionals
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched glass Shade

Width: 29-3/8 in
 Height: 8 in
 H/CTR: 5-13/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall or Ceiling	Prewired	Quantity: Three 18 W max. GU-24 or LED equivalent	CCSAus Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	GU24 base plastic sockets	1 year warranty
Canopy covers a standard 4" recessed outlet box: 5.3125" W., 0.875" ht., 5.3125" depth	120 V		