

One-Light Close-To-Ceiling

Wall or ceiling mounted • Damp location listed



Description:

Transit is a uniquely styled series with clean design flexibility. This one-light LED close to ceiling featuring a white acrylic diffuser and Antique Bronze finish can mount to either ceiling or wall.

Specifications:

- Antique Bronze (-20) (painted)
- Steel Construction
- White acrylic diffuser
- Replaceable LED module.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" - ADA
- ENERGY STAR® qualified

Performance:

| | |
|------------------------|---|
| Number of Modules | 1 |
| Input Power | 17w |
| Input Voltage | 120 V |
| Input Frequency | 60 Hz |
| Lumens/LPW (Source) | 1211/71.2 (LM-82) |
| Lumens/LPW (Delivered) | 776/45.1 (LM-79) |
| CCT | 3000 K |
| CRI | 90 CRI |
| Life (hours) | 60,000 (L70/TM-21) |
| FCC | Meets FCC Title 47, Part 15 Class B |
| Min. Start Temp | -30 °C |
| Max. Operating Temp | 30 °C |
| Warranty | 5 year warranty |
| Labels | cCSAus Damp location listed ENERGY STAR® qualified |

P3411-2030K9

Images:



Dimensions:

Square: 11"
 Depth: 3-3/4"
 Height: 3-3/4"
 H/CTR: 5.2"

P3411-2030K9

Dimming Notes:

P3411 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Verti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.