

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P3460-09

Melon

Two-light semi-flush with swirled alabaster glass and scroll arms. Perfect in entry ways, kitchen islands, closets and hallways.

- Two-light semi-flush.
- Swirled alabaster glass and scroll arms.
- Perfect in entry ways, kitchen islands, closets and hallways.

Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Alabaster glass bowl



Diameter: 13-1/4"

Height: 13-5/8"

Glass

Width: 13-1/4"

Height: 5-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling semi-flush mounted Mounting strap for outlet box included Canopy covers a standard 4" octagonal recessed outlet box 5.0625" W.	Pre-wired 6" of wire supplied 120 V	Quantity: Two 60w max. Medium Base E26 base ceramic sockets	UL-CUL Dry location listed 1 year warranty