

One-Light LED Flush Mount

Ceiling mounted • Damp location listed



P350004-009-30

Description:

One-light 19 inch LED Flush Mount in Brushed Nickel features an etched Alabaster glass bowl. Fixtures are dimmable to 10 percent with Triac, phase forward or ELV dimmers. 3000K and 90 CRI.

Specifications:

- Brushed Nickel (-009) (plated)
- Steel Construction
- Etched Alabaster glass bowl
- 1838 lumens 62 lumens/watt (delivered)
- 3000K color temperature, 90+ CRI
- TM-21 54,000 hour life.
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	30w
Input Voltage	120 V
Input Frequency	50/60 Hz
Lumens/LPW (Source)	2622/88 (LM-82)
Lumens/LPW (Delivered)	1838/62 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	54,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-25 °C
Max. Operating Temp	25 °C
Warranty	5 year warranty
Labels	ETL Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

Images:




Dimensions:

Diameter: 19"
Height: 8-3/4"

Progress Lighting

LED lighting facts®
A Program of the U.S. DOE

Light Output (Lumens)	1838
Watts	29.64
Lumens per Watt (Efficacy)	62.01
Color Accuracy <small>Color Rendering Index (CRI)</small>	90
Light Color <small>Correlated Color Temperature (CCT)</small>	3000 (Bright White)



2700K 3000K 4500K 6500K

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: TH64-32BMXJ (9/13/2016)
Model Number: P350004-009-30
Type: Luminaire - Decorative

P350004-009-30

Dimming Notes:

P350004 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron NTELV-300

Leviton 6681

Leviton 6672

Leviton 6674

Lutron AYCL-153P

Lutron AYLV-600P

Lutron NTLV-600

Lutron MAELV-601

Leviton AWRMG-EAW

Lutron N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.