

One-Light LED Flush Mount

Ceiling mounted • Damp location listed



Description:

One-light 19 inch LED Flush Mount in Antiques Bronze features a white linen glass bowl. Fixtures are dimmable to 10 percent with Triac, phase forward or ELV dimmers. 3000K and 90 CRI.

Specifications:

- Antique Bronze (-020) (painted)
- Steel Construction
- Etched White Linen glass bowl
- 1984 lumens 67 lumens/watt (delivered)
- 3000k color temperature, 90+ CRI
- TM-21 54,000 hour life.
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	30w
Input Voltage	120 V
Input Frequency	50/60 Hz
Lumens/LPW (Source)	2622/88 (LM-82)
Lumens/LPW (Delivered)	1984/67 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-25 °C
Max. Operating Temp	25 °C
Warranty	5 year warranty
Labels	ETL Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

P350008-020-30


Images:



Dimensions:

Diameter: 19"

Height: 7-1/8"



One-Light LED Flush Mount

Ceiling mounted • Damp location listed



P350008-020-30

Dimming Notes:

P350008 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron NTELV-300

Leviton 6681

Leviton 6672

Leviton 6674

Lutron AYCL-153P

Lutron AYL-600P

Lutron NTLV-600

Lutron MAELV-601

Leviton AWRMG-EAW

Lutron N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.