

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P350036-009

Debut

A new category of vintage modern fixtures takes center stage with this semi-flush, convertible fixture from one of our Design Series collections. Delicate details in a Brushed Nickel finish, create statement making focal pieces for a variety of interiors. Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades available in clear or frosted seeded finishes.

- Brushed Nickel finish.
- A uniquely vintage modern feel.
- Delicate details with a warm finish.
- Makes a great statement piece for a variety of interiors.
- Glass accessory shades in clear (P860003-001) or frosted (P860002-001) seeded finishes are available.
- Chain & ceiling mounts both included.

Category: Close-to-Ceiling

Finish: Brushed Nickel (plated)

Construction: Steel Construction



Diameter: 19-7/8"

Height: 15"

Overall Ht. W/Chain: 52"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Six feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5" W., 0.8125" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Three 60w max. Medium Base E26 base ceramic socket	cULus Dry location listed 1 year warranty