

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P350037-143

Gauge

Inspired by industrial elements, Gauge two-light flush mount features an open cage design that's both functional and aesthetically appealing. Frame is comprised of a Graphite finished wire frame with Brushed Nickel accents. Hinged door provides easy access to change lamp.

- Graphite finish with Brushed Nickel accents.
- Industrial inspired design.
- Features an open cage with hinged door.
- Shown with Vintage lamps (P7825-01).
- Brushed Nickel accents.

Category: Close-to-Ceiling

Finish: Graphite (painted)

Construction: Steel Construction



Diameter: 14"
Height: 6-3/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling mounted</p> <p>Mounting strap for outlet box included</p> <p>Unit covers a standard 4" octagonal recessed outlet box</p> <p>11.875" W., 1" ht., 11.875" depth</p>	<p>Pre-wired</p> <p>6" of wire supplied</p> <p>120 V</p>	<p>Quantity:</p> <p>Two 60w max. Medium Base</p> <p>E26 base ceramic socket</p>	<p>cCSAus Damp location listed</p> <p>1 year warranty</p>