

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P350039-020 Briarwood

The Briarwood collection features a classic pattern commonly found on barn or farmhouse doors and gates. The simple geometric form features a faux-painted wood enclosure to frame vintage-style light bulbs. A rich Oak and Antique Bronze finish combination. Two-Light flush mount.

- Features a classic pattern commonly found on barn or farmhouse doors and gates
- Faux-painted wood-look enclosure to frame vintage-style light bulbs.
- Rich, painted oaky finish paired with an Antique Bronze finish.

**Category:** Close-to-Ceiling

**Finish:** Antique Bronze (painted)

**Construction:** Steel Construction



Square: 12 in  
Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Flush-Mount mounted	Prewired	Quantity: Two 60 W max. Medium Base or LED equivalent	cCSAus Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	E26 base socket	1-year Limited Warranty
Fixture covers a standard 4" recessed outlet box: 11.25" W., 1.0625" ht., 11.25" depth	120 V		