

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P350039-143 Briarwood

The Briarwood collection features a classic pattern commonly found on barn or farmhouse doors and gates. The simple geometric form features a faux-painted wood enclosure to frame vintage-style light bulbs. A coastal-inspired whitewashed finish paired with Graphite details. Two-Light flush mount.

- Features a classic pattern commonly found on barn or farmhouse doors and gates
- Faux-painted wood enclosure to frame vintage-style light bulbs.
- Coastal-inspired whitewashed finish paired with Graphite details.

Square: 12 in
Height: 6 in

Category: Close-to-Ceiling
Finish: Graphite (painted)
Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Flush-Mount mounted	Prewired	Quantity:	cCSAus Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	Two 60 W max. Medium Base or LED equivalent	1-year Limited Warranty
Fixture covers a standard 4" recessed outlet box: 11.25" W., 1.0625" ht., 11.25" depth	120 V	E26 base socket	