PROGRESS LIGHTING

Project: Fixture Type: Location:

Contact:

P350046-163 Hansford

Hansford Collection One-Light Vintage Brass Clear Glass Farmhouse Flush Mount Light

Category: Close-to-Ceiling Finish: Vintage Brass (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Round



Diameter: 10 in Height: 12-1/29 in

Clear Glass Round Width: 10 in Height: 10 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling semi-flush	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5" W., 5" ht., 1.56" depth		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	