

LED Flush Mount

Flush-Mount Mounted • Damp Location Listed **PROGRESS LED**

Description:

One-Light 12-3/4" LED Flush Mount

Specifications:

- Etched Glass Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" recessed outlet box: 12.5 in W., 1.4375 in ht., 12.5 in depth
- Mounting plate for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	25 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	2,015/80 (LM-82)
Lumens/LPW (Delivered)	1,746/70.1 (LM-79)
CCT	3000 K
CRI	90+ CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2016

P350052-009-30



Dimensions:

Diameter: 12-1/2 in
 Height: 4-1/2 in

Etched Glass Diffuser
 Length: 10-11/16 in
 Width: 10-11/16 in
 Height: 3-3/4 in



P350052-009-30

Dimming Notes:

P350052-009-30 is designed to be compatible with many NEMA SSL 7a Phase Cut (forward phase) dimmers as well as many ELV (reverse phase) controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Caseta

Lutron_Ariadni AY-600P

Lutron_Lumea LG-603PG

Leviton_SureSlide 6672

Leviton_SureSlide 6674

Lutron_Ariadni AYCL-153P

Lutron_Skylark Contour CTCL-153P

Lutron_Diva DVCL-153P

Cooper Devine AL DAL06P

Lutron_Maestro MACL-153M

Lutron_Ariadni AYLV-600P

Lutron_Maestro MA-600

Lutron_Nova T NTLV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Lutron_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.