

Semi-Flush/Convertible

 Ceiling/Chain mounted • Damp location listed **PROGRESS LED**


Description:

Designed for both commercial and residential interiors, Apogee is an energy efficient, high performance LED fixture. All fixtures feature 120-277V input with standard dimming. Etched glass shade provides an even and pleasing light effect. Apogee is 3000K, 90+ CRI and meets California Title 24 - JA8 - 2016 standards and is ENERGY STAR rated and damp location listed. The Apogee Collection 21" LED Semi-Flush/Convertible is complimented by a Brushed Nickel finish.

Specifications:

- Brushed Nickel (-009) (plated)
- Steel Construction
- Etched Glass shade
- Semi-flush fixture convertible to hanging pendant with included hardware and instructions
- Commercial-grade construction and performance
- Features Brushed Nickel finish
- Etched glass shade provides an even and pleasing light effect
- Features 41-watt integrated LED to deliver energy savings and reduce long-term maintenance costs
- 3000K color temperature, 90CRI
- 120-277V operation, 0-10V compatible dimming
- 2765 lm, 67.1 Lum/Watt
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 15 feet of wire supplied
- Six feet of 9 gauge chain supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	41w
Input Voltage	120-277 V
Input Frequency	60 Hz
Lumens/LPW (Source)	
Lumens/LPW (Delivered)	2765/69.3 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	58,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class A
Min. Start Temp	-30 °C
Max. Operating Temp	30°C
Warranty	5 year limited warranty
Labels	cETLus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

P350065-009-30

Images:



Dimensions:

Diameter: 21"
Height: 14-1/2"
Overall Ht. W/Chain: 92"

Glass
Width: 18-5/8"
Height: 3"

P350065-009-30**Dimming Notes:**

P350065 is designed to be compatible with many 0-10V controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NFTV

Lutron - NTFTV

Lutron - DDTV

Leviton - AWSMT-7DW

Leviton - IP710

Lithonia ISD BC

Pass & Seymour - CD4FB

Wattstopper ADF-120277

Hunt Dimming - PS-010-120V

Hunt Dimming - PS010 277V

Lightolier Controls - MP1500FAM120

Lightolier Controls - ZP600FAM120

Synergy Lighting Controls - V2000FAMU

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.