

Maier LED

Wall or Ceiling Mounted • Damp Location Listed PROGRESS LED



Description:

14" LED flush mount with etched white opal acrylic diffuser with a clean modern look. 3000K color temperature and 90+ CRI. Acrylic bowl is attached with a twist and lock action for ease of installation. This fixture can be mounted on ceiling or wall. ENERGY STAR and Title 24. Brushed Nickel finish.

Specifications:

- White acrylic Diffuser
- Etched white opal acrylic diffuser.
- Acrylic bowl is attached with a twist and lock action.
- Can be mounted on ceiling or wall.
- Dimmable to 10% with many ELV dimmers
- Acrylic diffuser twists into the frame so there are no exposed fasteners for a clean modern look.
- 2500 lumens, 78.1 lumen/watt (delivered)
- 3000K color temperature, 90CRI
- Energy Star Qualified
- Meets California T24 JA8-2016.
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" recessed outlet box: 13.625 in W., 1.3125 in ht., 13.625 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	32 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2,500/78.1 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	36000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	ETL Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

P350077-009-30



Dimensions:

Diameter: 14 in
Height: 4-3/4 in

**Dimming Notes:**

P350077-009-30 is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T VTELV-300

Lutron_Diva DVELV-300P

Lutron_Diva DVCL-253P

Lutron_Caseta Wireless

Lutron_Ariadni AYCL-153P

Lutron_Toggler TGCL-153PH

Lutron_NTLV-600

Lutron_Maestro MAELV-601

Lutron_Nova N-600

Leviton_SureSlide 6674

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P350077-009-30