

Project:		
Fixture Type:		
Location:		
Contact:		

Ceiling mounted • Damp location listed PROGRESS LED





### **Description:**

Featuring a sleek and slim appearance, the 160in. flush mount from the Bezel LED Collection is an architectural flush mount. Etched white glass is accented by a metal trim in a Polished Chrome finish. The glass shade is illuminated on both the bottom and sides to provide a pleasing lighted effect.

# P350087-015-30

#### Images:

## **Specifications:**

- Polished Chrome (-015) (plated)
- Steel Construction
- Etched White glass Bowl
- Features a sleek and slim appearance inspired by architectural design
- · The glass shade is illuminated on both the bottom and sides to provide a pleasing lighted effect
- · Fits seamlessly within Modern, Traditional and Transitional interiors
- Polished Chrome finish
- · Measured 16in diameter x 4-3/4in ht.
- Contains one 26W LED Module 1,142 lumens 44 lumens/watt (delivered), 3000K color temperature, 90+ CRI.
- · CSA Safety listed for use in damp locations
- Compatible with many ELV dimmers
- · ENERGY STAR certified
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- · Includes installation instructions and mounting hardware
- Dimmable to 10% brightness (See Dimming Notes)
- Fixture covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016



#### **Dimensions:**

Diameter: 16" Height: 4-3/4"

Glass

Width: 15-5/16" Height: 3-13/16"

### Performance:

Number of Modules	1
Input Power	26w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1770/68.07692307692308 (LM-82)
Lumens/LPW (Delivered)	1142/43.7 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30°C
Warranty	5 year limited warranty
Labels	cCSAus Damp location listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016









P350087-015-30

## **Dimming Notes:**

P350087 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls**

Lutron - NTEVL-300 Lutron - DVELV-300P Lutron - Caseta Wireless Leviton – 6672 Leviton - 6674 Lutron - AYCL-153P Lutron - AYLV-600P Lutron - MAELV-601 Leviton - AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.