

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P350090-020 Glayse

Inspired by modern architecture. Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function. The four-light semi-flush convertible fixture is complimented by an Antique Bronze finish.

- Inspired by modern architecture
- The structure of Glayse is the focal point of the design, where form follows function
- Four light semi flush convertible
- Popular Antique Bronze finish
- The frameless unbounded beveled glass creates beautiful light and reflection
- Uses four 60-watt max. medium base bulbs (sold separately)
- Glayse features handsome details for variety of interior design styles
- A natural choice for closets, hallways and smaller areas within the home.

Square: 16-3/4 in  
Height: 14 in  
Depth: 16-3/4 in  
Overall Ht. W/Stem: 80 in

Clear glass Beveled Panel  
Width: 15-3/8 in  
Height: 6-3/4 in

**Category:** Close-to-Ceiling

**Finish:** Antique Bronze (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Clear glass Beveled Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Semi-Flush Convertible	10 feet of wire supplied	Quantity: four 60 W max. A-19 or LED equivalent	cULus Dry Location Listed
Mounting strap for outlet box included	120 V	E26 base	1-year Limited Warranty
Two pieces of six links of 9 gauge chain supplied			
two 6", eight 12" lengths of stem included			
canopy covers a standard 4" recessed outlet box: 7.5" W., 1" ht., 7.5" depth			