

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P350107-31M

### Clifton Heights

Clifton Heights Collection 12-3/4" Two-Light Modern Farmhouse Matte Black Etched Glass Semi-Flush Mount Light

**Category:** Close-to-Ceiling

**Finish:** Matte Black (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Etched Glass Square/Rectangular

Width: 12-3/4 in  
Square: 12-3/4 in  
Height: 11 in

Etched Glass Square/Rectangular  
Width: 12-3/4 in  
Height: 4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(2) Medium Base (E26) Lamp Type A19	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 1.12" ht., 4.75" depth		Fully dimmable with dimmable bulbs	