

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



P350116-071

Foster

Brighten a living room, hallway, bedroom, or wherever overhead lighting is needed with a pinch of antique design with the Foster two-light flush mount. Iron metal arms hold the juxtaposed light bulbs inside the piece, creating a structure that is open, yet intimate. A taste of mixed metal elements makes the fixture ideal for industrial and vintage interiors.

Diameter: 16"
Height: 6"
Depth: 16"

- Just right for living rooms, hallways, bedrooms, or wherever overhead lighting with a touch of antique detailing is desired
- Flush mount with rounded, iron metal arms
- Juxtaposed bulbs are tucked inside the open, yet intimate, design
- Squared lines and mixed metal elements are ideal for industrial and vintage settings
- Exposed bulbs held by decorative sockets add a vintage charm
- Gilded Iron finish complements the fixture's clean ironwork styling
- A round, circular base provides a solid foundation for the design
- Measures 16 in diameter X 6 in height
- Uses two 60-watt max medium base bulbs, or the LED equivalent, that are sold separately
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

Category: Close-to-Ceiling

Finish: Gilded Iron (Painted)

Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting Plate for outlet box included Ceiling Pan covers a standard 4" octagonal recessed outlet box 13" W., 13" ht., 1" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Two 60w max. Medium Base E26 base Porcelain sockets	cETLus Dry location listed