

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P350117-141

Gulliver

The four-light semi-flush fixture that can also convert to a hanging fixture in the Gulliver Collection features arching and delicate details that curve to create an airy design. Dual toned frame color combinations in a Galvanized finish with antique white accents The hand painted wood grained texture finished to emulate weathered driftwood complements Rustic and Modern Farmhouse home decor, as well as Urban Industrial and Coastal interior settings.

- Gulliver's deftly painted two-toned metal frame reads like a rustic wood finish
- The distinguished four-light semi-flush convertible fixture is an ideal choice for a library or home office
- entry vestibule or masculine bedroom
- Its rustic styling is ideal for Coastal or Farmhouse spaces
- Galvanized Finish with banding that resembles sun-bleached wood
- Measures 14 7/8in diameter x 12 5/8in ht.
- Includes hanging and ceiling-mount hardware
- Uses four, 60-watt max candelabra bulbs or LED equivalent (sold separately) vintage bulbs are an option for a rustic look
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Close-to-Ceiling Finish: Galvanized Finish (painted) Construction: Steel Construction



Diameter: 15-1/4" Height: 12-5/8"

Overall Ht. W/Chain: 53"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Flush-Mount mounted	Pre-wired	Quantity:	cETLus Dry location listed
Mounting plate for outlet box included Three feet of 9 gauge chain supplied	10 feet of wire supplied 120 V	Four 60w max. Candelabra Base E12 base phenolic sockets	1 year warranty
Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 5.125" ht., 0.875" depth			