

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P350117-143

Gulliver

The four-light semi-flush fixture that can also convert to a hanging fixture in the Gulliver Collection features arching and delicate details that curve to create an airy design. Dual toned frame color combinations in a Graphite finish with weathered oak accents The hand painted wood grained texture complements Rustic and Modern Farmhouse home decor, as well as Urban Industrial and Coastal interior settings.



Diameter: 15-1/4"
Height: 12-5/8"
Overall Ht. W/Chain: 53"

- Gulliver's deftly painted two-toned metal frame reads like a rustic wood finish
- The distinguished four-light semi-flush convertible fixture is an ideal choice for a library or home office
- entry vestibule or masculine bedroom
- Its rustic styling is ideal for Coastal or Farmhouse spaces
- Graphite Finish with banding that resembles weathered gray-stained wood
- Measures 14 7/8in diameter x 12 5/8in ht.
- Includes hanging and ceiling-mount hardware
- Uses four, 60-watt max candelabra bulbs or LED equivalent (sold separately) vintage bulbs are an option for a rustic look
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Close-to-Ceiling

Finish: Graphite (painted)

Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Flush-Mount mounted Mounting plate for outlet box included Three feet of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 5.125" ht., 0.875" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Four 60w max. Candelabra Base E12 base phenolic sockets	cETLus Dry location listed 1 year warranty