

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P350122-143

Rainey

The Rainey Collection three-light semi-flush convertible embraces an artful display of asymmetrical design styling. A slender, staggered frame representing organic forms draws the eye upward to admire the clear fluted ribbed glass shades. The larger scale is suitable for open floor plans, great rooms or anywhere a dramatic focal piece is needed to make a bold statement. The Graphite finish is paired with Brushed Bronze accents.

- A modern study in asymmetrical design, the Rainey features a staggered frame that represents abstracted organic forms
- The three-light, semi-flush convertible fixture features fluted, ribbed glass shades
- The light's smaller scale makes it appealing for foyers, breakfast nooks, guest rooms or a dressing room
- Its contemporary sophistication is a natural choice for Modern, Mid-Century and Luxe interiors
- Graphite finish with brushed bronze accents
- Measures 18in diameter x 16in ht.
- Includes ceiling-mount and hanging hardware
- Uses 3, 60-watt max. candelabra base bulbs including LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



Diameter: 18"
Height: 16"
Overall Ht. W/Chain: 81-1/2"

Width: 1-15/16"
Height: 7-1/2"

Category: Close-to-Ceiling

Finish: Graphite (plated)

Construction: Steel Construction

Glass/Shade: Clear Fluted Ribbed glass Shades

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Flush-Mount mounted Mounting plate for outlet box included Six links of 9 gauge chain supplied Canopy covers a standard 4" octagonal recessed outlet box 4.75" W., 0.875" ht., 4.75" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Three 60w max. Candelabra Base E12 base phenolic sockets	cCSAus Dry location listed 1 year warranty