

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P350130-143

Inspire

Harkening back to a simpler time, the Inspire Collection freshens traditional forms with flowing lines. The two-light flush mount fixture features an etched glass diffuser with a summer linen shade finished with Graphite details. This fixture is suitable for a variety of design styles, including Modern, Traditional and Farmhouse and the simple design is a perfect complement to a variety of fixture collections.

- Gives a dash of flair to the standard ceiling light
- Summer Linen shade with an etched glass diffuser gives a beautiful glow of light
- Close-to-ceiling lights like this two-light flush mount are natural choices for bathrooms, closets, hallways, and small rooms
- Fits seamlessly within Modern, Traditional and Farmhouse interiors
- Dramatic Graphite finish
- Measured 13in diameter x 10 1/8in ht.
- Uses two 75-watt max. base lamps or LED equivalent (sold separately)
- UL Safety listed for use in damp locations
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available



Diameter: 13"
Height: 5-1/2"

Glass
Width: 12-5/8"
Height: 0-1/8"
Glass 2
Width: 4-1/2"
Length: 13"
Height: 13"

Category: Close-to-Ceiling

Finish: Graphite (painted)

Construction: Steel Construction

Glass/Shade: Fabric Shade Diffuser

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted covers a standard 4" octagonal recessed outlet box 8.25" W., 1" ht., 8.25" depth	6" of wire supplied 120 V	Quantity: Two 60w max. Medium Base E26 base porcelain sockets	cULus Damp location listed 1 year warranty Meets California Title 24 high efficacy requirements for outdoor use