

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P350142-081

Point Dume™ - Sequit Point

The romance and architectural presence of a lighthouse is expressed in the Sequit Point group. In the same way strips of glass increased the effectiveness of lighthouse beacons, the modern Sequit Point series benefits from a similar ingenuity. Mercury glass sleeves stand in tandem with clear glass rods and an Antique Nickel finish to provide a familiar glow for the convertible ceiling fixture/ pendant. This family of fixtures is part of Jeffrey Alan Marks Point Dume™ lighting collection which celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences.

Category: Close-to-Ceiling

Finish: Antique Nickel (plated)

Construction: Steel Construction

Glass/Shade: Mercury glass Cylindrical



Diameter: 14"
Height: 9-5/8"
Depth: 14-3/8"
Overall Ht. W/Stem: 78"

Glass

Width: 9-13/16"

Height: 8-1/2"

Glass 2

Width: 0-3/8"

Length: 0-3/8"

Height: 8-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem mounted Mounting plate for outlet box included Six links of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 0.8125" ht., 5.125" depth	Pre-wired 10 feet of wire supplied 120 V	Quantity: Three 60w max. Candelabra Base E12 base Phenolic sockets	cETLus Dry location listed 1 year warranty