

Project: Fixture Type:

Location: Contact:





P350148-031

Bowman

Beautiful lighting will appeal to both your classic taste and your artistic spirit with this semi-flush convertible from the Bowman Collection. Wandering eyes will focus on the clear, chiseled glass shade that encircles elegant light sources gathering quietly at the light fixture's center. Handsome, black light bases with sophisticated curved arms originate from a decorative black knob that embellishes the outer bottom of the textured glass shade.

- · Beautiful lighting will appeal to both your classic taste and your artistic spirit with this semiflush convertible.
- Wandering eyes will focus on the clear, chiseled glass shade that encircles elegant light sources gathering quietly at the light fixture's center.
- · Handsome, black light bases with sophisticated curved arms originate from a decorative black knob that embellishes the outer bottom of the textured glass shade.
- · Ideal for any hallway, foyer, stairway, or kitchen.
- · Perfect for transitional, rustic, farmhouse, or coastal settings.
- Measures 14-1/4-inch width by 13-3/8-inch height.
- Uses three candelabra base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Close-to-Ceiling Finish: Matte Black (Painted) Construction: Steel Construction

Glass/Shade: Clear Chiseled glass bell shaped shade

Diameter: 14-1/4 in Height: 13-3/8 in Overall Ht. W/Chain: 52-1/2 in

Clear Chiseled glass bell shaped shade Width: 13-7/8 in Height: 7-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity: Three 60 W max. Candelabra	CCSAus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	Base or LED equivalent	1-year Limited Warranty
3 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			