

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P350148-151 Bowman

This Three-Light Cottage White Semi-Flush Convertible from the Bowman Collection will appeal to both your classic taste and your artistic spirit. Wandering eyes will focus on the clear chiseled glass shade that encircles elegant light sources gathering quietly at the light fixture's center. Cottage white light bases with sophisticated curved arms originate from a decorative knob that embellishes the out bottom of the textured glass shade. The light fixture can hang from a chain or be mounted flush to the ceiling.

- Clear chiseled glass shade encircles elegant light sources gathering quietly at the light fixture's center.
- Cottage white light bases with sophisticated curved arms originate from a decorative knob that embellishes the outer bottom of the textured glass shade.
- Can hang from a chain or be mounted flush to the ceiling.
- Ideal for any hallway, foyer, stairway, or kitchen.
- Perfect for transitional, rustic, farmhouse, or coastal settings.
- Measures 14-1/4-inch width by 13-3/8-inch height.
- Uses three candelabra base bulbs that are sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Diameter: 14-1/4 in
Height: 13-3/8 in
Overall Ht. W/Chain: 52-1/2 in

Clear Chiseled glass bell shaped shade
Width: 13-7/8 in
Height: 7-1/4 in

Category: Close-to-Ceiling

Finish: Cottage White (Painted)

Construction: Steel Construction

Glass/Shade: Clear Chiseled glass bell shaped shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CCSAus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	Three 60 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
3 feet of 9 gauge chain supplied	120 V	E12 base Phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			