## **PROGRESS** LIGHTING<sup>™</sup>

Project:

Fixture Type:

Location:

Contact:

## P350152-031 Dwyer

Incorporate a vintage feel with a dash of industrial personality with this flush mount. An attention-grabbing, clear ribbed glass shade takes center stage in this design, creating a gaslight glow when the fixture is illuminated. A simple metal frame coated in a black finish encases the glass to emphasize the collection's chic industrial edge.

- An attention-grabbing, clear ribbed glass shade takes center stage in this design, creating a gaslight glow when the fixture is illuminated.
- A simple metal frame coated in a black finish encases the glass to emphasize the collection's chic industrial edge.
- $\boldsymbol{\cdot}$  Incorporate a vintage feel with a dash of industrial personality with this flush mount.
- Ideal for any hallway, foyer, stairway, or kitchen.
- $\cdot\,$  Perfect for transitional, contemporary, or luxury settings.
- Measures 11-inch width by 4-inch height.
- Uses two medium base bulbs that are sold separately (60w max LED or incandescent).
- $\cdot\,$  Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Close-to-Ceiling Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Ribbed glass Panel, Clear Ribbed Glass Panel



Square: 11 in Height: 4 in

Clear Ribbed glass Panel Width: 10-1/2 in Height: 10-1/2 in

Clear Ribbed Glass Panel Width: 10-1/2 in Height: 3-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: Two 60 W max. Medium Base or	CCSAus Damp Location Listed
1/8 IP mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
Coiling Pan covors a standard 4"	120 V	E26 base Porcelain sockets	

Ceiling Pan covers a standard 4" recessed outlet box: 11" W., 0.75" ht., 11" depth