

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P350153-009 Winslett

Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful craftsmanship of this semi-flush mount. Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean, crisp lines coated in a gorgeous brushed nickel finish. Lightly seeded glass shade rest in shiny pedestal light bases that add an unexpected, but welcomed dash of modern personality to this clean, traditional design.

- Lightly seeded glass shade rest in shiny pedestal light bases that add an unexpected, but welcomed dash of modern personality to this clean, traditional design.
- Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean, crisp lines coated in a gorgeous brushed nickel finish.
- Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the semi-flush mount's beautiful craftsmanship.
- Ideal for any hall, foyer, stairways, or kitchen.
- Perfect for transitional, rustic, farmhouse, or coastal settings.
- Measures 13-3/4-inch width by 11-7/8-inch height.
- Use three candelabra base bulb that is sold separately (60w max - LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Diameter: 13-3/4 in
Height: 11-7/8 in
Overall Ht. W/Chain: 50-1/2 in

Clear Seeded glass Cylindrical Shade
Width: 13-3/4 in
Height: 8-1/8 in

Category: Close-to-Ceiling

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Clear Seeded glass Cylindrical Shade

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain/Semi-Flush	Prewired	Quantity: three 60 W max. B-10 or LED equivalent	cCSAus Dry Location Listed
Mounting plate for outlet box included	10 feet of wire supplied	E12 base Phenolic sockets	1-year Limited Warranty
3 feet of 9 gauge chain supplied	120 V		
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth			