PROGRESS LIGHTING[™]

Project: Fixture Type: Location:

Contact:

P350167-012 Inspire

Inspire Collection 18" Three-Light Transitional Satin Brass Summer Linen Semi-Flush Mount Light

Category: Close-to-Ceiling Finish: Satin Brass (Plated) Construction: Steel Construction Glass/Shade: Summer Linen Fabric Drum Shade, Diffuser Glass Disc



Diameter: 18 in Height: 11-1/2 in

Summer Linen Fabric Drum Shade Width: 18 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5.187" W., 1.437" ht., 5.187" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	